



YAV1CL2BOX, Uninsulated Ring Terminal For 1 AWG, 1-Hole, 5/16" Stud

By Burndy

Catalog # [YAV1CL2BOX](#)

Pure Electrolytic Copper Ring Tongue Terminal, 1 AWG, 5/16 IN Stud, Electro-Tin Plated, Die index: 42

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

Industrials, Hospitals, Utilities, Marine, Computer

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Industry Standard(s)	• UL467 • Military Specified (Mil-Spec)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	1
Conductor - Copper Str Aircraft Size	AN 1
Conductor - Copper Str Aircraft Size Range	AN 1
Conductor Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor Type	• CU C Solid-Size



- CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.76 in
Package Height	0.000 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - Strip Length inch	5/8 in
Dimension - Stud Size inch	5/16
Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.60 in
Dimension - Z inch	0.38 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Length Overall inch	1.84 in
Dimension - D inch	0.76 in
Dimension - N inch	0.38 in

General

Die Index	42
Trade Name	HYLUG™
Material Composition	• DLP Copper • Tin Plating
Military Specification	AS20659
Physical Attribute - Tongue Type	Ring
Application - For Use On	Copper Commercial (Code) Cable, Type AN Aircraft Cable, Extra Flexible Conductors
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived

Type	Ring Tongue	Logistics	
UPC 14 Digit GTIN	00781810539804	Minimum Pack Quantity	1
Material	Copper	Carton Quantity	10
Plating Type	Tin		
UPC	781810539804	Product Assets	



A Hubbell brand

[Catalog \[English\]](#)