

YAV2402M14, Compression Terminal

By Burndy
Catalog # [YAV2402M14](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Compatible Standards: IEC61238-1, UL 486A-468B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance CM
Status

Conductor

Conductor - Material COPPER
Conductor Size 240 mm²
Conductor Type CLASS 2

Configuration

Number of Pad Holes 2
Connector Type METRIC

Current

Voltage Rating 35 kV
Voltage - Maximum 35000

Dimensions

Dimension - Pad Width inch 1.55 in
Package Height 0.000 in
Dimension - Hole Size fraction 1/2
Package Weight 0.000 lb.

Package Length 0.000 in
Package Width 0.000 in
Dimension - L Length Overall mm 126 mm
Dimension - Hole Size mm 14 mm
Dimension - Hole Size inch 0.56
Dimension - Strip Length inch 1.30 in
Dimension - Stud Size fraction 1/2
Dimension - Bolt Size fraction 1/2
Physical Attribute - Tongue Straight
Angle
Dimension - Z inch 0.57 in
Dimension - B Length inch 1.27 in
Dimension - Bolt Size inch 0.5
Dimension - Length Overall inch 4.96 in

General

Trade Name HYLUG™
Die Index 20
Plated Y
UPC 781810357620
Type Metric Terminals
Material Copper
Plating Type Tin - Electro Plated
Finish Type Tin-Plated
UPC 12 Digit 781810357620
UPC 14 Digit GTIN 00781810357620

Logistics

Minimum Pack Quantity 5
Pallet Quantity 4800
Carton Quantity 5

Product Assets

[Catalog \[English\]](#)