



YAV26L2NK, Compression Terminal, 2/0 AWG, 1-Hole, 5/16" Stud, Standard Barrel, Nickel Plated

By Burndy
Catalog # [YAV26L2NK](#)



HYLUG™ Copper Compression Terminal; 1 Hole with Inspection Window, AN-2/0 Aircraft, 600V-35kV, 5/16" stud, Seamless

Features

- Seamless, heavy duty uninsulated compression terminal provides a strong connector for demanding applications requiring high reliability
- Suitable for use on Type AN aircraft cable, extra flexible conductors and commercial (code) conductors

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Str Aircraft Size	00 Aircraft
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.934 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.48 in
Dimension - B Length inch	0.782 in
Dimension - N inch	0.467 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	2.319 in

General

Trade Name	HYLUG™
Die Index	13
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Yes
UPC	781810139714
Type	Standard Barrel, Nickel Plated
Material	Copper
Plating Type	Nickel
Finish Type	Nickel Plated
UPC 12 Digit	781810139714
UPC 14 Digit GTIN	00781810139714

Logistics

Minimum Pack Quantity	100
Pallet Quantity	23200
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)