



YAV26L43NK, Uninsulated Ring Terminal For 2/0 AWG, 1-Hole, 3/8" Stud, Nickel Plated

By Burndy
Catalog # [YAV26L43NK](#)

Uninsulated Ring Terminal For 2/0 AWG (Nickel Plated)

Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft	AN-2/0
Size	
Conductor Size	2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of	1
Holes	



Connector Type	Ring Terminal
----------------	---------------

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.78 in
Dimension - Z inch	0.48 in
Dimension - Pad Width inch	0.83 in
Physical Attribute - Tongue	Straight
Angle	
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size mm	10 mm
Dimension - Stud Size inch	3/8 in
Dimension - Length Overall	2.27 in
inch	
Dimension - N inch	0.41 in

General

Die Index	44
Physical Attribute - Tongue	Ring
Type	
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810370612
Material	Copper
Plating Type	Nickel
UPC	781810370612

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	29000

Product Assets

[Catalog \[English\]](#)