

YAV240M10, Compression Terminal

By Burndy
Catalog # [YAV240M10](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Compatible Standards: IEC61238-1, UL 486A-468B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance CM
Status

Conductor

Conductor - Material COPPER
Conductor Size 240 mm²
Conductor Type CLASS 2

Configuration

Physical Attribute - Number of 1
Holes
Number of Pad Holes 1
Connector Type METRIC

Current

Voltage Rating 35 kV
Voltage - Maximum 35000

Dimensions

Dimension - Pad Width inch 1.55 in
Package Height 0.000 in
Dimension - Hole Size fraction 3/8
Package Weight 0.000 lb.
Package Length 0.000 in
Package Width 0.000 in
Dimension - L Length Overall 72.9 mm

Dimension - Outside Diameter 1.06 in
inch
Dimension - Hole Size mm 10.4 mm
Dimension - Hole Size inch 0.41
Dimension - Strip Length inch 1.27 in
Dimension - Stud Size inch #10
Dimension - Stud Size fraction 3/8
Dimension - Bolt Hole Size inch 0.41 in
Dimension - Bolt Size fraction 3/8
Physical Attribute - Tongue Straight
Angle
Dimension - Z inch 0.42 in
Dimension - B Length inch 1.27 in
Dimension - D inch 0.90 in
Dimension - N inch 0.41 in
Dimension - Inside Diameter 0.83 in
inch
Dimension - Bolt Size inch 0.38
Dimension - Length Overall 2.87 in
inch

General

Trade Name HYLUG™
Die Index 20
Feature - Barrel Type Standard
Feature - Barrel Style Chamfered
Plated Y
UPC 781810322420
Type Metric Terminals
Material Copper
Plating Type Tin - Electro Plated
Finish Type Tin-Plated
UPC 12 Digit 781810322420
UPC 14 Digit GTIN 00781810322420

Logistics

Minimum Pack Quantity 5
Pallet Quantity 7680
Carton Quantity 10

Product Assets

[Catalog \[English\]](#)