



YAV2CL58, Seamless Terminal, #2 AWG, 1-Hole, M10 Stud

By Burndy
Catalog # [YAV2CL58](#)

Heavy Duty Right-AngleTerminals.

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer N
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	N
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Aircraft Size Range	N/A
Conductor - Copper Str Navy Size Range	N/A
Conductor Size	2 AWG



Conductor - Copper Str Size Range	N/A
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Ring Terminal
----------------	---------------

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Hole Size mm	0 mm
Dimension - Thread Size	-

General

Sub Brand	HYLUG
Die Index	41
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG
Plated	Y
Feature - Barrel Style	Chamfered
Construction Material - Main	Copper
Insulation	N
Type	YAV-L
UPC 12 Digit	781810538968
UPC 14 Digit GTIN	00781810538968
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC	781810538968

Logistics

Minimum Pack Quantity	100
Carton Quantity	50
Pallet Quantity	48000

Product Assets

[Catalog \[English\]](#)