



YAV2CL56, Seamless Terminal, #2 AWG, 1-Hole, 1/2" Stud

By Burndy
Catalog # [YAV2CL56](#)

Heavy Duty Right-AngleTerminals.



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - ETL	No
Certification - UL Recognized	N
Standards - RoHS Compliance Status	CM
Buy American Compliant	Contact Manufacturer
Certification - cULus	N
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	2 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Number of Pad Holes	1
Connector Type	Ring Terminal

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Thread Size	-
Dimension - Hole Size mm	0 mm

General

Feature - Barrel Style	Chamfered
Plated	Y
Trade Name	HYLUG
Physical Attribute - Tongue Type	Ring
Sub Brand	HYLUG
Die Index	41
UPC	781810510902
Type	YAV-L
Insulation	N
Construction Material - Main Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810510902
UPC 14 Digit GTIN	00781810510902

Logistics

Minimum Pack Quantity	50
Pallet Quantity	48000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)