

YAV352M10, Compression Terminal

By Burndy
Catalog # [YAV352M10](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	35 mm ² , 2 AWG
Conductor Size	35 mm ²
Conductor Type	CLASS 2

Configuration

Number of Pad Holes	2
Connector Type	METRIC

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	17.3 in
Package Height	0.000 in

Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	91 mm
Bolt Size	M10
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Thickness - Pad	0.10 in
Dimension - Strip Length inch	0.67 in
Dimension - Stud Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.42 in
Dimension - B Length inch	16.0 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.57 in

General

Trade Name	HYLUG™
Die Index	10
Plated	Y
UPC	781810636503
Type	Metric Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810636503
UPC 14 Digit GTIN	00781810636503

Logistics

Minimum Pack Quantity	50
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)