

YAV400F2M20, Compression Terminal

By Burndy
Catalog # [YAV400F2M20](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	400 mm2
Conductor - Material	COPPER
Conductor Type	CLASS 2

Configuration

Number of Pad Holes	2
Connector Type	METRIC

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.98 in
----------------------------	---------

Dimension - Hole Size fraction	7/8
Dimension - Bolt Size fraction	7/8
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.89 in
Dimension - L Length Overall mm	149 mm
Dimension - B Length inch	1.42 in
Dimension - Hole Size mm	23.8 mm
Dimension - Bolt Size inch	0.88
Dimension - Hole Size inch	0.94
Dimension - Length Overall inch	5.88 in
Dimension - Strip Length inch	1.46 in
Dimension - Stud Size fraction	7/8

General

Plated	Y
Trade Name	HYLUG™
Die Index	24
UPC	781810641132
Type	Metric Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810641132
UPC 14 Digit GTIN	00781810641132

Logistics

Minimum Pack Quantity	5
-----------------------	---

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)