



YAV4CL3NK, Uninsulated Ring Terminal For 4 AWG, 1-Hole, #10 Stud, Nickel Plated

By Burndy

Catalog # [YAV4CL3NK](#)

Uninsulated Ring Terminal For 4 AWG (Nickel Plated)



Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Application

For use on: Type AN aircraft cable, extra flexible conductors and commercial(code) conductors, Applications include aircraft, industrials, hospitals, electric utilities, marine, computers, and other equipment subject to vibration or requiring dependable electrical performance

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	4
Conductor - Copper Solid Size	4
Conductor - Copper Str Aircraft Size	AN 4
Conductor Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.55 in
Package Height	0.000 in
Dimension - Hole Size mm	5 mm
Dimension - Strip Length inch	1/2
Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.2 in
Dimension - Bolt Size fraction	#10
Dimension - Length Overall inch	1.37 in
Dimension - N inch	0.25 in

General

Die Index	40
Trade Name	HYLUG™
Sub Brand	TERMINALS, HYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810088227
Material	Copper
Plating Type	Nickel
UPC	781810088227

Logistics

Minimum Pack Quantity	200
Carton Quantity	200
Pallet Quantity	79200



A Hubbell brand