



YAV8CL1NK, Uninsulated Ring Terminal For 8 AWG (Nickel Plated)

By Burndy
Catalog # [YAV8CL1NK](#)

Uninsulated Ring Terminal For 8 AWG (Nickel Plated)



Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	8 AWG
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size	8 AWG
Range	
Conductor Type	• CU C Str-Size • CU C Str Aircraft-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type

Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Length Overall inch	1.19 in
Dimension - D inch	0.58 in
Dimension - N inch	0.25 in

General

Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 12 Digit	781810085684
UPC 14 Digit GTIN	00781810085684
Material	Copper
Plating Type	Nickel
UPC	781810085684

Logistics

Minimum Pack Quantity	1
Carton Quantity	200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)