



YBM26L2, Uninsulated Flag-Type Ring
Terminal For 2/0 AWG

By Burndy
Catalog # [YBM26L2](#)

Uninsulated Flag-Type Ring Terminal For 2/0 AWG

Features

- Made of pure electrolytic copper for maximum conductivity and ductility
- Seamless extrusion tin plated to resist corrosion
- Beveled barrel for easy wire entry

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	AN 2/0
Conductor Size	2/0 AWG
Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flag Ring Terminal

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.78 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Z inch	0.45 in
Dimension - Pad Width inch	0.84 in
Physical Attribute - Tongue Angle	90 Degree
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Stud Size inch	1/4 in
Dimension - Length Overall inch	1.66 in
Dimension - N inch	0.33 in

General

Die Index	598
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Style	Chamfered
UPC 14 Digit GTIN	00781810455586
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810455586

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	24000

Product Assets

[Catalog \[English\]](#)