

YCA262NG6W, Copper compression terminal for terminating to switch pads, 2/0 Str, 2-hole, 1/2" Stud, 1-3/4" Spacing, Hot Tin Plated

By Burndy

Catalog # [YCA262NG6W](#)

Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 2/0 Str., 1/2 IN Stud, 2 Pad holes, Hot tin plated

Features

- Copper Compression Terminal designed for terminating copper conductor to switch pads
- 2/0 Str, 1/2" Stud, 2 Pad Holes
- Hot tin plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - Copper Str Size	2/0 AWG

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.97 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-18/25 in
Dimension - Z inch	0.65 in



Dimension - L Length Overall mm	135 mm
Dimension - B Length inch	1.72 in
Dimension - Outside Diameter inch	0.71 in
Dimension - D inch	3.03 in
Dimension - N inch	0.63 in
Dimension - Inside Diameter inch	0.45 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.30 in
Dimension - Strip Length inch	1 13/16

General

Plated	Y
Trade Name	HYLUG™
Die Index	K-5/8-1
UPC	781810088722
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810088722
UPC 14 Digit GTIN	00781810088722

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)