



YCA262NTN, Copper compression terminal, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Tin Plated

By Burndy
Catalog # [YCA262NTN](#)

Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 2/0 Str., 1/2 IN Stud, 2 Pad holes, Tin plating

Features

- Copper Compression Terminal Designed for terminating Copper Conductor to Switch Pads
- 2/0 Str, 1/2" Stud, 2-Pad Holes
- Tin plating

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	2/0 AWG
-----------------------------	---------

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.97 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-18/25 in
Package Weight	0.000 lb.
Package Length	0.000 in



Package Width	0.000 in
Dimension - Z inch	0.62 in
Dimension - L Length Overall mm	134 mm
Dimension - B Length inch	1.72 in
Dimension - Outside Diameter inch	0.71 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.27 in
Dimension - Strip Length inch	1 3/16
Dimension - Stud Size inch	1/2

General

Plated	Y
Trade Name	HYLUG™
Die Index	• 166 • 206
UPC	781810216026
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810216026

Logistics

Minimum Pack Quantity	25
Pallet Quantity	5800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)