



YC3L12, Cu Compression C-Tap, Thin Wall

By Burndy
Catalog # [YC3L12](#)

Copper Compression C Tap, Thin Wall, 5-4 AWG (Run), 6-5 AWG (Tap)



Features

- Material is high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Bare copper range taking connector allows for less inventory
- Reinforced ribs on the outside of the connector increase the mechanical strength of the connection
- Creates a compact connection that is easy for taping and insulating
- Connectors are clearly marked with color code dot, UL and CSA (when applicable), wire size, and die index number

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor Size	3 AWG-12 AWG
Conductor - Copper Str Run Range	3 AWG-5 AWG
Conductor - Copper Str Run	3 AWG-5 AWG
Conductor Type	CODE
Conductor - Copper Str Tap Range	5 AWG-12 AWG
Conductor - Copper Str Tap	5 AWG-12 AWG

Configuration

Connector Type C-TAP

Current

Voltage - Maximum 35000

Dimensions

Dimension - Pad Width inch	0.27 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Strip Length inch	1-3/16
Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.46 in
Dimension - D inch	1.18 in

General

Trade Name	CRIMPIT™
Die Index	11
Plated	Y
Color Code	Green
Sub Brand	CRIMPIT
UPC	781810040140
Type	YC-L Series
Material	Copper
Plating Type	Tin - Bright
Finish Type	Tin-Plated
UPC 12 Digit	781810040140
UPC 14 Digit GTIN	00781810040140

Logistics

Minimum Pack Quantity	1
Pallet Quantity	57600
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)