



YCA26RL2N, Al compression terminal, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 2/0

By Burndy
Catalog # [YCA26RL2N](#)



Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus,Die index:659

Features

- Aluminum Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Cmpt Size Range	2/0 AWG
Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/0 (6/1) Quail AWG
Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG
Conductor Type	- ACSR C Str-Size - AAC

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
----------------	----------

Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.83 in
Dimension - L Length Overall mm	168 mm
Dimension - Pad Width inch	1.12 in
Package Height	0.000 in
Dimension - B Length inch	2.70 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall inch	6.62 in

General

Die Index	659
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Plated	N
UPC 12 Digit	781810810446
UPC 14 Digit GTIN	00781810810446
Material	Aluminum
Plating Type	Unplated
UPC	781810810446

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	7400

Product Assets

[Catalog \[English\]](#)