



YCA272N, Copper compression lug, 3/0 Str, 2-hole, 1-3/4" Spacing

By Burndy
Catalog # [YCA272N](#)

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus

Features

- Copper Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	3/0 AWG
-----------------------------	---------

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.79 in
Dimension - L Length Overall mm	135 mm
Dimension - Pad Width inch	1.08 in
Package Height	0.000 in



Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Strip Length inch	1 13/16
Dimension - Stud Size inch	1/2
Dimension - B Length fraction	1-20/29 in
Dimension - B Length inch	1.69 in
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight
Dimension - Length Overall inch	5.33 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in

General

Die Index	167
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	N
Physical Attribute - Tongue Type	Standard
Plated	N
UPC 14 Digit GTIN	00781810886724
Material	Copper
Plating Type	Unplated
UPC	781810886724

Logistics

Minimum Pack Quantity	1
Carton Quantity	6
Pallet Quantity	4608

Product Assets

[Catalog \[English\]](#)