



YCA252N, Cu Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA252N](#)



Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 5-3/8 IN L

Features

- NEMA Standard mounting holes
- Made of pure copper

Application

Designed for terminating copper conductors to switch pads and other substation or switch yard apparatus

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.91 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/9
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	136 mm
Dimension - Outside Diameter inch	0.62 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	1 5/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-4/7 in
Dimension - Z inch	2.37 in
Dimension - B Length inch	1.57 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	5.34 in

General

Trade Name	HYLUG™
Die Index	165
Prefilled Oxide Inhibitor	N
Plated	No
Physical Attribute - Tongue Type	Standard
Sub Brand	TERMINALS, HYLUG
Product Type	Compression
UPC	781810810385
Type	YCA-2N
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810810385
UPC 14 Digit GTIN	00781810810385

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)