



YCA25RL2N, Al compression terminal, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 1/0

By Burndy
Catalog # [YCA25RL2N](#)



Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus,Die index: C, 247, 702

Features

- Aluminum Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Cmpt Size Range	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor Type	- ACSR C Str-Size - AAC

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.80 in
Dimension - L Length Overall mm	176 mm
Dimension - Pad Width inch	1.12 in
Package Height	0.000 in
Dimension - B Length inch	3.03 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall inch	6.91 in

General

Die Index	247 702 - C
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Plated	N
UPC 12 Digit	781810810422
UPC 14 Digit GTIN	00781810810422
Material	Aluminum
Plating Type	Unplated
UPC	781810810422

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	9800

Product Assets

[Catalog \[English\]](#)