

YCA282NTN, Copper compression terminal, 2-hole, 1/2" Stud, 1-3/4" Spacing, Tin Plated

By Burndy
Catalog # [YCA282NTN](#)



Cu Compression terminal, 2 Holes, 4/0 (7,12,19) AWG STR, 1/2 IN Stud, 1.75 IN Spacing, 168 or 208 Index, Tin plated

Features

- Copper Compression Terminal
- 2-Hole Pad
- 4/0 (7, 12, 19) AWG Str
- 1/2" Stud, 1-3/4" Spacing
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.22 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-69/100 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.62 in
Dimension - L Length Overall mm	136 mm
Dimension - B Length inch	1.62 in
Dimension - Outside Diameter inch	0.89 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.35 in
Dimension - Strip Length inch	1 11/16
Dimension - Stud Size inch	1/2

General

Plated	Y
Trade Name	HYLUG™
Die Index	• 168 • 208
UPC	781810055793
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810055793

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)