



YCA262NDTS, Copper compression terminal for terminating Copper conductor to switch pads, 2/0 Str, 1/2" Stud, 1-3/4" Spacing, Sealed oil tight and tin plated.

By Burndy
Catalog # [YCA262NDTS](#)

Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 2/0 Str., 1/2 IN Stud, 2 Pad holes, Sealed oil tight and tin plated

Features

- Copper Compression Terminal designed for terminating copper conductors to switch pads
- 2/0 Str, 1/2" Stud
- 2 Pad Holes
- Sealed oil tight and tin plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	2/0 AWG
-----------------------------	---------

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions



Dimension - Pad Width inch	0.97 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length inch	1.72 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Strip Length inch	1-13/16 in
Dimension - Stud Size inch	1/2 in

General

Plated	Y
Trade Name	HYLUG™
Die Index	166
UPC	781810170168
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810170168

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)