



YCA28R2N, Al Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 4/0 AWG

By Burndy
Catalog # [YCA28R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 6.83 IN L

Features

- Aluminum compression HYLUG
- NEMA Standard Mounting Holes

Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
----------------	----------



Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.88 in
Dimension - L Length Overall mm	173 mm
Dimension - Pad Width inch	1.21 in
Package Height	0.000 in
Dimension - B Length inch	2.80 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall inch	6.83 in

General

Die Index	249 11A - K-840
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCA-R-N
UPC 12 Digit	781810810477
UPC 14 Digit GTIN	00781810810477
Material	Aluminum
Plating Type	Unplated
UPC	781810810477

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	8100

Product Assets

[Catalog \[English\]](#)