



YCA26R2N, Al compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 2/0

By Burndy
Catalog # [YCA26R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 6.30 IN L

Features

- Aluminum Compression HYLUG, 2-hole NEMA 1/2" Stud, 1-3/4" Spacing

Application

For ACSR/6201/5005 (Compressed/Compact), Aluminum

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/0 (6/1) Quail AWG
Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
----------------	----------



Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.70 in
Dimension - L Length Overall mm	160 mm
Dimension - Pad Width inch	0.97 in
Package Height	0.000 in
Dimension - B Length inch	2.43 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall inch	6.30 in

General

Die Index	245 9A
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINAL,TERMINALS
Plated	N
Type	YCA-R-N, Terminal
UPC 12 Digit	781810810439
UPC 14 Digit GTIN	00781810810439
Material	Aluminum
Plating Type	Unplated
UPC	781810810439

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	9800

Product Assets

[Catalog \[English\]](#)