

YCA292N, Copper compression Lug, 2-hole pad, 1/2" Stud, 1-3/4" Spacing. Used to terminate copper conductor to switch pads and other apparatus

By Burndy
Catalog # [YCA292N](#)

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 5.52 IN L

Features

- NEMA Standard mounting holes
- Made of pure copper

Application

Designed for terminating copper conductors to switch pads and other substation or switch yard apparatus

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/9
Package Weight	0.000 lb.



Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	140 mm
Dimension - Outside Diameter inch	0.95 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	1 7/8
Dimension - Stud Size inch	33/64
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1- 81/100 in
Dimension - B Length inch	1.81 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	5.52 in

General

Trade Name	HYLUG™
Die Index	169
Oxide Inhibitor Type	Penetrox A
Prefilled Oxide Inhibitor	Y
Plated	No
Physical Attribute - Tongue Type	Standard
Sub Brand	TERMINALS, HYLUG
Product Type	Compression
UPC	781810014790
Type	YCA-2N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014790

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2320
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)