



YCA282N90,Copper Overhead Compression Terminal, 4/0 AWG, 2-Hole, 90 Degree Angle Tongue

By Burndy
Catalog # [YCA282N90](#)

Cu Overhead Compression Terminal Designed for terminating Cu
Conductors to Switch Pads, 4/0 AWG, 2 Pad Holes, 90 Deg, 168
Index

Features

- Copper Overhead Compression Terminal designed for terminating copper conductors to switch pads
- 4/0 AWG, 2 Pad Holes
- 90 Degree

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.22 in
Dimension - Hole Size fraction	5/9



Physical Attribute - Tongue Angle	90 Degree
Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Outside Diameter inch	0.89 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	1 11/16
Dimension - Stud Size inch	33/64

General

Plated	N
Trade Name	HYLUG™
Die Index	• 168 • 208
Oxide Inhibitor Type	Penetrox A
UPC	781810289259
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810289259
UPC 14 Digit GTIN	00781810289259

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2304
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)