

YCA292NDTS, Copper overhead compression terminal, 250 kcmil, 2-Hole, cable to pad, 1/2" Stud, 1-3/4" Spacing, Sealed oil tight and tin plated

By Burndy

Catalog # [YCA292NDTS](#)

Cu Overhead Compression Terminal, 250 Kcmil Cu Cable, 2 Pad Holes, Cable To Pad, 169 Index, Sealed Oil Tight And Tin Plated

Features

- Copper Overhead Compression Terminal
- 250 kcmil Copper Cable
- 2 Pad Holes
- Sealed Oil Tight and Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	250 kcmil
Range	
Conductor - Copper Str Size	250 kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.28 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight



Dimension - B Length fraction	1- 81/100 in
Dimension - Z inch	0.65 in
Dimension - L Length Overall mm	140 mm
Dimension - B Length inch	1.81 in
Dimension - D inch	3.03 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.52 in
Dimension - Strip Length inch	1 13/16

General

Plated	Y
Trade Name	HYLUG™
Die Index	169
UPC	781810085097
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810085097

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2775
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)