



YCA322N, Copper compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing.

By Burndy
Catalog # [YCA322N](#)

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 6.72 IN L

Features

- Copper Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.67 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	171 mm



Dimension - Outside Diameter inch	1.24 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	2 5/8
Dimension - Stud Size inch	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.62 in
Dimension - B Length inch	2.78 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.72 in

General

Trade Name	HYLUG™
Die Index	209
Prefilled Oxide Inhibitor	N
Plated	N
Physical Attribute - Tongue Type	Standard
UPC	781810014738
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014738

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1110
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)