



YCA292NTN, Cu Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 250 kcmil

By Burndy
Catalog # [YCA292NTN](#)

Cu Wire lug, 250 kcmil, .56"stud, 5.52"L



Features

- Copper Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	250 kcmil
Range	
Conductor - Copper Str Size	250 kcmil

Configuration

Physical Attribute - Number of	1
Crimps Required	
Physical Attribute - Number of	2
Holes	
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.28 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue	Straight
Angle	
Dimension - B Length fraction	1- 81/100 in

Dimension - L Length Overall	140 mm
mm	
Dimension - B Length inch	1.81 in
Dimension - Outside Diameter	0.95 in
inch	
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall	5.52 in
inch	
Dimension - Strip Length inch	1 7/8
Dimension - Stud Size inch	33/64

General

Plated	Y
Trade Name	HYLUG™
Die Index	169
Oxide Inhibitor Type	Penetrox A
UPC	781810413005
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810413005

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2960
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)