



YCA37R2N, Al Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA37R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 8.15 IN L

Features

- Aluminum compression HYLUG
- NEMA Standard Mounting Holes

Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	477 (24-7) kcmil 477 (26-7) kcmil 477 (30-7) kcmil, 556.5 (18-1)
Conductor - ACSR Str Size Range	477 (24-7) kcmil 477 (26-7) kcmil 477 (30-7) kcmil, 556.5 (18-1)
Conductor - AL Str Size	556 kcmil
Conductor - AL Str Size Range	556 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal



Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	207 mm
Dimension - Pad Width inch	1.94 in
Package Height	0.000 in
Dimension - B Length inch	3.65 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	8.15 in

General

Die Index	261
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCA-R-N
UPC 12 Digit	781810810705
UPC 14 Digit GTIN	00781810810705
Material	Aluminum
Plating Type	Unplated
UPC	781810810705

Logistics

Minimum Pack Quantity	1
Carton Quantity	20
Pallet Quantity	2880

Product Assets

[Catalog \[English\]](#)