

YCA312N, Cu Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA312N](#)

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, Index: 267

Features

- NEMA Standard mounting holes
- Made of pure copper

Application

Designed for terminating copper conductors to switch pads and other substation or switch yard apparatus

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.63 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25 in
Package Weight	0.000 lb.
Package Length	0.000 in



Package Width	0.000 in
Dimension - L Length Overall mm	166 mm
Dimension - Outside Diameter inch	1.17 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	2 3/4
Dimension - Stud Size inch	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.62 in
Dimension - B Length inch	2.66 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	6.55 in

General

Trade Name	HYLUG™
Die Index	267
Prefilled Oxide Inhibitor	N
Plated	No
Physical Attribute - Tongue Type	Standard
Sub Brand	TERMINALS, HYLUG
Product Type	Compression
UPC	781810014837
Type	YCA-2N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014837

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1470
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)