

YCAB394N, Copper compression lug 4-Hole pad, 1/2" Stud, 1-3/4" Spacing. Used for terminating copper conductor to switch pads and other apparatus

By Burndy
Catalog # [YCAB394N](#)

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, Die Index: 627

Features

- NEMA Standard mounting holes
- Made of pure copper

Application

Designed for terminating copper conductors to switch pads and other substation or switch yard apparatus

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor


Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25 in
Package Weight	0.000 lb.
Package Length	0.000 in



Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	217 mm
Dimension - Outside Diameter inch	1.7 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	3 1/16
Dimension - Stud Size inch	33/64
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.63 in
Dimension - B Length inch	3 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	8.53 in

General

Trade Name	HYLUG™
Die Index	627
Oxide Inhibitor Type	Penetrox A
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	TERMINALS, HYLUG
UPC	781810014868
Type	YCAB-4N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014868

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)