



YCAK31AG1, Al alloy teminal, 2-hole, 350 kcmil Cu/Al/Compact

By Burndy
Catalog # [YCAK31AG1](#)

Cast Aluminum Alloy Terminal, 2 Pad Holes, 350 kcmil Cu,Al Conc.& Compact, 317, 705 Index

Features

- Aluminum Alloy Terminal
- 2-Hole

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil
Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil

Configuration

Physical Attribute - Pad Configuration	1 Hole
--	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	1.94 in
Dimension - L Length Overall mm	115 mm

Dimension - Pad Width inch	1.25 in
Physical Attribute - Tongue Angle	Straight
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	4.52 in
Dimension - D inch	1.31 in

General

Die Index	317 705
Physical Attribute - Tongue Type	Standard
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810810224
UPC 14 Digit GTIN	00781810810224
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC	781810810224

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand