



YCA321RL2N, Al compression lug for terminating overhead conductors to switch pads, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA321RL2N](#)

Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus, Die index:655

Features

- NEMA Standard Mounting Holes
- Pre-filled with PENETROX joint compound, stripsealed and capped to limit oxide growth and increase the life of the connection

Application

Used for terminating overhead conductors to switch pads and other substation or switch yard apparatus.

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Cmpt Size Range	336.4 kcmil
Conductor - ACSR Str Size	336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	336 kcmil
Conductor Type	• ACSR C Str-Size • AAC

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions



Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	1.13 in
Dimension - L Length Overall mm	165 mm
Dimension - Pad Width inch	1.59 in
Package Height	0.000 in
Dimension - B Length inch	2.25 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall inch	6.50 in

General

Die Index	655
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Plated	N
Type	YCA-RL-2N
UPC 12 Digit	781810810743
UPC 14 Digit GTIN	00781810810743
Material	Aluminum
Plating Type	Unplated
UPC	781810810743

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	3920

Product Assets

[Catalog \[English\]](#)