



YCAK321R4N, Al compression lug, 4-Hole,
1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCAK321R4N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 7.09 IN L

Features

- Aluminum Compression Lug, NEMA Standard 4-Hole Pad, 1/2" Stud, 1-3/4" Spacing

Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified Certification - ETL	Contact Manufacturer No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	336.4 (18-1) kcmil
Conductor - ACSR Str Size Range	336.4 (18-1) kcmil
Conductor - AL Str Size	336.4 kcmil 350 kcmil
Conductor - AL Str Size Range	336.4 kcmil - 350 Kcmil

Configuration

Physical Attribute - Pad Configuration	4 Hole NEMA
--	-------------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	180 mm
Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - B Length inch	2.74 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	7.09 in

General

Die Index	321
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL, TERMINAL
Plated	N
Type	YCAK-R-N
UPC 12 Digit	781810810255
UPC 14 Digit GTIN	00781810810255
Material	Aluminum
Plating Type	Unplated
UPC	781810810255

Logistics

Minimum Pack Quantity	1
Carton Quantity	15
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)