



YCA361R2N, Al compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA361R2N](#)



AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 7.69 IN L

Features

- Aluminum compression HYLUG
- NEMA Standard Mounting Holes

Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Buy America(n) Qualified Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	477.0 (18-1) kcmil
Conductor - ACSR Str Size Range	477.0 (18-1) kcmil
Conductor - AL Str Size	477 kcmil
Conductor - AL Str Size Range	477 kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	195 mm
Dimension - Pad Width inch	1.82 in
Package Height	0.000 in
Dimension - B Length inch	3.24 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	7.69 in

General

Die Index	327
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCA-R-N
UPC 12 Digit	781810016718
UPC 14 Digit GTIN	00781810016718
Material	Aluminum
Plating Type	Unplated
UPC	781810016718

Logistics

Minimum Pack Quantity	15
Carton Quantity	30
Pallet Quantity	3600

Product Assets

[Catalog \[English\]](#)