

YCAK35R4N, Al compression lug, 4-Hole 1/2" Stud, 1-3/4" Spacing

By Burndy

Catalog # [YCAK35R4N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 7.34 IN L

Features

- Aluminum Compression Lug, NEMA Standard 4-Hole Pad, 1/2" Stud, 1-3/4" Spacing

Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Buy America(n) Qualified Certification - ETL	No
Standards - RoHS Compliance Status	Contact Manufacturer
Certification - CSA Approved	CM
UL Listed	No

Conductor

Conductor - ACSR Str Size	397.5 (26/7) Ibis kcmil 397.5 (30/7) Larkspur kcmil
Conductor - ACSR Str Size Range	397.5 kcmil (26-7,18-1,30-7 STR)
Conductor - AL Str Size	397 kcmil
Conductor - AL Str Size Range	397 kcmil

Configuration

Physical Attribute - Pad Configuration	4 Hole NEMA
--	-------------



Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	187 mm
mm	
Dimension - Pad Width inch	3 in
Package Height	0.000 in
Dimension - Hole Size inch	0.56 in
Dimension - B Length inch	3.05 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall	7.34 in
inch	

General

Die Index	317
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCAK-R-N
UPC 12 Digit	781810016756
UPC 14 Digit GTIN	00781810016756
Material	Aluminum
Plating Type	Unplated
UPC	781810016756

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	1120

Product Assets

[Catalog \[English\]](#)