



YCA392N, Copper compression lug for terminating copper conductors to switch pads and other apparatus, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Sealed oil tight and tin plated.

By Burndy
Catalog # [YCA392N](#)

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 2 Hole



Features

- Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size	750 kcmil
Range	

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	2.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	14/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	183 mm

Dimension - Outside Diameter inch	1.7 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	3 1/16
Dimension - Stud Size inch	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.62 in
Dimension - B Length inch	3.00 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Length Overall inch	7.22 in

General

Trade Name	HYLUG™
Die Index	627
Prefilled Oxide Inhibitor	N
Plated	N
Physical Attribute - Tongue Type	Standard
UPC	781810810729
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810810729

Logistics

Minimum Pack Quantity	1
Pallet Quantity	588
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)