



YCA39R2N, Al Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA39R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 8.31 IN L

Features

- Aluminum compression HYLUG
- NEMA Standard Mounting Holes

Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Buy America(n) Qualified Certification - ETL	No
Standards - RoHS Compliance Status	Contact Manufacturer
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	• 556.5 kcmil (24-7) • 556.5 kcmil (26-7)
Conductor - ACSR Str Size Range	556.5 (24-7) kcmil -556.5 (26-7) kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal



Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	211 mm
Dimension - Pad Width inch	2.08 in
Package Height	0.000 in
Dimension - B Length inch	3.59 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	8.31 in

General

Die Index	608
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCA-R-N
UPC 12 Digit	781810016688
UPC 14 Digit GTIN	00781810016688
Material	Aluminum
Plating Type	Unplated
UPC	781810016688

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)