



YCHC29TC2, Compression C-Tap

By Burndy

Catalog # [YCHC29TC2](#)

Copper Compression C Tap, 250 kcmil- 2 AWG (Main), 2-6 AWG (Tap 1), 8-14 AWG (Tap 2), Tin Plated



Features

- Range taking C-tap that allows for less inventory as one C-tap can accommodate a multitude of wire combinations
- Manufactured from high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex M Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex K Run Range	2 AWG-4/0 AWG
Conductor Size	250 KCMIL-2 AWG
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Run	250 KCMIL-2 AWG
Conductor - Copper Solid Tap	• 6 • 5 • 4 • 3 • 2
Conductor Type	CODE/FLEX
Conductor - Copper Flex I Run Range	2 AWG-4/0 AWG
Conductor - Copper Str Tap Range	2 AWG-6 AWG



A Hubbell brand

Conductor - Copper Str Tap2 AWG-6 AWG

Configuration

Connector TypeC-TAP

Current

Voltage - Maximum35000

Dimensions

Package Height	0.000 in
Dimension - Height inch	1.78 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	21 mm
Dimension - Strip Length inch	1 in
Dimension - Width inch	0.97 in
Dimension - Length Overall inch	0.81 in

General

Trade Name	CRIMPIT™
Die Index	251
Plated	Y
Color Code	Red
Sub Brand	CRIMPIT
UPC	781810013755
Type	YCHC Series
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810013755
UPC 14 Digit GTIN	00781810013755

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8880
Carton Quantity	60

Product Assets

[Catalog \[English\]](#)