



YDS2C, Copper Single Sleeve Full Tension Splice



By Burndy
Catalog # [YDS2C](#)

CU Full Tension Splice, Accommodates Wire: #2 Cu STR (Hard, Medium, or Soft Drawn), Die Index: 163

Features

- Copper Full Tension Sleeve for Copper Conductors
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Stranded Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	2 AWG
-----------------------------	-------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	94 mm
Dimension - Outside Diameter inch	0.50 in
Dimension - B Length fraction	1-18/25 in
Dimension - B Length inch	1.72 in
Dimension - Length Overall inch	3.69 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Die Index	163
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810820902
Type	YDS - C
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810820902

Logistics

Minimum Pack Quantity	100
Pallet Quantity	14800
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)