



YDS6WK, Copper Full Tension Splice

By Burndy
Catalog # [YDS6WK](#)



CU Full Tension Splice, Accommodates Wire: #6 Sol COPPERWELD,
Die Index: 162 or 276

Features

- Copper Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Copperweld Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	6 AWG
Conductor - CopperWeld Solid Size	6 AWG
Range	
Conductor - CopperWeld C Solid Size	6 AWG
Conductor - Copper Str Size	1 AWG

Configuration

Physical Attribute - Number of	6
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	103 mm
Dimension - B Length inch	1.77 in
Dimension - Outside Diameter inch	0.48 in
Dimension - Length Overall inch	4.04 in

General

Plated	No
Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Sub Brand	HYSPLICE
Die Index	• 276 • 162
Product Type	Compression
UPC	781810014585
Type	YDS-K
Prefilled Oxide Inhibitor	N
Construction Material - Main Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014585

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7200
Carton Quantity	150

Product Assets

[Catalog \[English\]](#)