



YDS31AT, Aluminum Full Tension Splice

By Burndy
Catalog # [YDS31AT](#)



Full tension splice made of aluminum tubing with staked -in cable stop. Designed for all aluminum conductor. ANSI C119.4 Class 1 (Full Tension)

Features

- Aluminum Full Tension Splice
- Staked in Cable Stop

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	350 (19) kcmil
Conductor - ACAR Str Size	350 (19) kcmil
Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil
Conductor Type	- ACSR C Str-Size - AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	5-16/39 in
-------------------------------	------------

Dimension - L Length Overall mm	278 mm
Dimension - B Length inch	5.41 in
Dimension - Outside Diameter inch	1.12 in
Dimension - Length Overall inch	10.95 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	490
UPC	781810015650
Prefilled Oxide Inhibitor	Y
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015650
UPC 14 Digit GTIN	00781810015650

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2520
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)