



YDS34, Copper Single Sleeve Full Tension Splice



By Burndy
Catalog # [YDS34](#)

CU Full Tension Splice, Accommodates Wire: 500 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 210

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Stranded Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	500 kcmil
-----------------------------	-----------

Configuration

Physical Attribute - Number of	5
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	295 mm
Dimension - Outside Diameter inch	1.38 in
Dimension - B Length fraction	5-3/4 in
Dimension - B Length inch	5.75 in
Dimension - Length Overall inch	11.62 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Die Index	210
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810014677
Type	YDS
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014677

Logistics

Minimum Pack Quantity	1
Pallet Quantity	585
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)