

YDS375H, Full Tension Steel Splice

By Burndy
Catalog # [YDS375H](#)

Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension), Die index:304

Features

- Full-Tension HYSPLICE Sleeve, made of hot-dip galvanized seamless milled steel tubing, lined with silicone carbide particles

Application

For HS, EHS, Utilities (UT) Or Siemens-Martin (SM) Galvanized Steel Guy, Messenger, And Static Conductors

Specifications


Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Grade	HS, UT
Conductor - Galvanized Steel Str Size	3/8 (7) in
Conductor - Galvanized Steel Str Size Range	3/8 (7) in
Conductor - AL Coated Steel Size Range	3/8 (7) in
Conductor - AL Coated Steel Size	3/8 (7) in
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------



Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	230 mm
mm	
Dimension - Outside Diameter	0.75 in
inch	
Dimension - B Length fraction	4-17/81 in
Dimension - B Length inch	4.21 in
Dimension - Length Overall	9.07 in
inch	

General

Trade Name	HYSPLICE™
Die Index	304
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810016015
Type	YDS-H
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810016015
UPC 14 Digit GTIN	00781810016015

Logistics

Minimum Pack Quantity	25
Pallet Quantity	1872
Carton Quantity	13

Product Assets

[Catalog \[English\]](#)