



YDS4C, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # YDS4C

CU Full Tension Splice, Accommodates Wire: #4 Cu STR (Hard, Medium, or Soft Drawn), Die Index: 162

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Stranded Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	4 AWG
-----------------------------	-------

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	65 mm
Dimension - Outside Diameter inch	0.40 in
Dimension - B Length fraction	1-3/20 in
Dimension - B Length inch	1.15 in
Dimension - Length Overall inch	2.55 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Die Index	162
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810821060
Type	YDS - C
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810821060

Logistics

Minimum Pack Quantity	1
Pallet Quantity	34800
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)