



YF2012IWL, Covered Ferrule For 20 AWG

By Burndy
Catalog # [YF2012IWL](#)

Covered Ferrule For 20 AWG



Features

- Made of electrolytic copper, tin plated
- Smooth funnel entry to make wire insertion easier
- Secure contacting even after multiple reconnections
- Long-term contact resistance
- No fraying of strands
- No breakage of wire strands when wire is bent, under stress, or in vibration environment
- UL listed per UL486F requirements
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	20 AWG
----------------	--------

Conductor - Copper Solid Size	20 AWG
Conductor - Copper Str Size	20 AWG

Configuration

Connector Type	End Termination
----------------	-----------------

Dimensions

Dimension - D1 inch	0.05 in
Dimension - D2 inch	0.11 in
Dimension - D inch	0.06 in
Dimension - Length Overall inch	0.71 in

General

Plated	Y
UPC	621945621800
Type	Bootlace Ferrule
Insulation	Y
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	500
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)