



YDS7M9T, Full Tension Sleeve for Alumoweld

By Burndy
Catalog # [YDS7M9T](#)



Full Tension Sleeve, 7 #9, 3 #6, 10-3/8 in L, Full-tension splice for Alumoweld transmission lines

Features

- Full-Tension splice for Alumoweld transmission lines
- Five connectors accommodate eight conductor sizes
- Sleeve is pre-filled with PENETROX Joint Compound and Capped
- Sleeve is high strength aluminum alloy for optimum corrosion resistance

Application

For Alumoweld Transmission Lines, Sleeve Is High Strength Aluminum Alloy For Optimum Corrosion Resistance

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	RUS
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AWAC Size	2
Conductor - Alumoweld Size Range	• 7#9 • 3#6
Conductor - Alumoweld Size	• 7#9 • 3#6

Configuration

Connector Type Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	264 mm
Dimension - Outside Diameter inch	0.8 in
Dimension - B Length fraction	5-7/50 in
Dimension - B Length inch	5.14 in
Dimension - Length Overall inch	10.41 in

General

Trade Name	HYSPLICE™
Die Index	677
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	FULL TENSION SLEEVE, HYSPLICE
UPC	781810015438
Type	YDS-M-T
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015438

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3360
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)