



YFTW0814DL, Covered Twin Ferrule For 8 AWG

By Burndy
Catalog # [YFTW0814DL](#)

Covered Twin Ferrule For 8 AWG

Features

- Made of electrolytic copper, tin plated
- Smooth funnel entry to make wire insertion easier
- Secure contacting even after multiple reconnections
- Long-term contact resistance
- No fraying of strands
- No breakage of wire strands when wire is bent, under stress, or in vibration environment
- UL listed per UL486F requirements
- RoHS Compliant

Application


For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	8 AWG
----------------	-------



Conductor - Copper Solid Size	8 AWG
Conductor - Copper Str Size	8 AWG

Configuration

Connector Type	End Termination
----------------	-----------------

Dimensions

Dimension - D1 inch	0.25 in
Dimension - D2 inch	0.51 in
Dimension - D inch	0.27 in
Dimension - Length Overall inch	1.02 in

General

Plated	Y
UPC	621945623132
Type	Bootlace Ferrule
Insulation	Y
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)