




YF0818IDL, Covered Ferrule For 8 AWG

By Burndy
Catalog # [YF0818IDL](#)

Covered Ferrule For 8 AWG



Features

- Made of electrolytic copper, tin plated
- Smooth funnel entry to make wire insertion easier
- Secure contacting even after multiple reconnections
- Long-term contact resistance
- No fraying of strands
- No breakage of wire strands when wire is bent, under stress, or in vibration environment
- UL listed per UL486F requirements
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	8 AWG
----------------	-------

Conductor - Copper Solid Size	8 AWG
Conductor - Copper Str Size	8 AWG

Configuration

Connector Type	End Termination
----------------	-----------------

Dimensions

Dimension - D1 inch	0.18 in
Dimension - D2 inch	0.30 in
Dimension - D inch	0.19 in
Dimension - Length Overall	1.10 in

General

Plated	Y
UPC	621945622432
Type	Bootlace Ferrule
Insulation	Y
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)