



YG14BTC26 Compression Bus Bar Connector

By Burndy
Catalog # [YG14BTC26](#)

Copper Compression Bus Bar Connector, 1/4 " Thick Steel and
Copper Busbar to 2/O AWG - # 2 AWG Str

Features

- Compression Busbar Connector
- Easier to use than Exothermic Connections
- Ideally suited for cellular tower applications.

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • UL 486A • CSA C22.2 No 65
Standards - RoHS Compliance Status	CM
Certification - cULus	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A • CSA C22.2 No 65
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Tap Range	2 AWG-2/O AWG
Conductor - Copper Flex G Tap	• 2 AWG • 1 AWG • 1/O AWG • 2/O AWG
Conductor - Copper Solid Run	1/4" bus bar
Conductor - Copper Solid Tap Range	1 AWG-1/O AWG
Conductor - Copper Solid Tap	• 1 AWG • 1/O AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • Bar-Size

Conductor - Copper Str Tap Range	2 AWG-2/O AWG
Conductor - Copper Str Tap	• 2 AWG • 1 AWG • 1/O • 2/O AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Dimension - B Length fraction	64/79 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.81 in

General

Plated	N
Trade Name	HYGROUND®
UPC	781810267806
Prefilled Oxide Inhibitor	Y
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810267806
UPC 14 Digit GTIN	00781810267806

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5800
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)